




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD/PIGTAIL LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	09-09-09	EFK		RELEASED TO PRODUCTION	02779-63				



FIBER OPTIC 900um BUFFERED LC PIGTAIL CUSTOMER DRAWING	
	<b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (.3) ±.010   ANGLES
DRAWN BY EFK	REVIEW DRAWING NUMBERS
DATE 09-09-09	PART NO. SEE SHEET 2
CHK'D	DRAWING NO. 02779-63 SHEET 1 OF 2
	SCALE NONE
	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FIBER OPTIC 900 $\mu$ m BUFFERED LC PIGTAIL							
PANDUIT PART NO.	CABLE				CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5B10-NM*	RISER (OFNR)	50/125 $\mu$ m	SIMPLEX 900 $\mu$ m BUFFERED FIBER	BLUE	0.25dB	20dB	BLACK
F6B10-NM*		62.5/125 $\mu$ m					ELECTRIC IVORY
FXB10-NM*		10GbE OM3			0.25dB	26dB	AQUA
FXOB10-NM*		OPTIMIZED 10GbE OM3					
FZB10-NM*		10GbE OM4			0.25dB	26dB	AQUA
FZOB10-NM*		OPTIMIZED 10GbE OM4					
F9B10-NM*		9/125 $\mu$ m OS1			0.35dB	55dB	BLUE

\* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	09-09-09	EFK		RELEASED TO PRODUCTION	02779-63				

FIBER OPTIC 900 $\mu$ m BUFFERED LC PIGTAIL CUSTOMER DRAWING									
				<b>PANDUIT</b> <sup>TM</sup> CORP. TINLEY PARK, ILL 60477					
 THIRD ANGLE PROJECTION				ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (0.3) ±.010   ANGLES				DRAWING FILENAME M02779CZ_DC/01A	
				AS NOTED				SCALE NONE	
				DRAWN BY EFK				PART NO. SEE TABLE	
				DATE 09-09-09				DRAWING NO. 02779-63	
				CHK'D				SHEET 2 OF 2	
								SIZE <b>A</b>	