



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

LC CONNECTOR HOUSING KEY CONFIGURATIONS		
"A" BLACK	"B" RED	"C" GREEN
"D" YELLOW	"E" ORANGE	"F" DARK BLUE


										FIBER OPTIC PATCH CORD DUPLEX SC TO KEYED LC CONFIGURATION CUSTOMER DRAWING				
											 TINLEY PARK, ILL 60477			
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME	
											DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (.0.3) (.XX) ±.03 (.0.8) ANGLES		SCALE	
										DRAWN BY MC	REVIEW DRAWING NUMBERS		PART NO.	
													SEE TABLE, SHT. 2	
R	10-25-07	MC		RELEASED TO PRODUCTION	02779-51					DATE 10-01-07			DRAWING NO.	SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D			02779-51	A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX SC TO KEYED LC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				SC CONNECTORS			KEYED LC CONNECTORS		
	FIBER TYPE	RATING	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	KEY/COLOR
F5E3-10AM** F5E3-10BM** F5E3-10CM** F5E3-10MD** F5E3-10ME** F5E3-10MF**	50/125um OM2	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F6E3-10AM** F6E3-10BM** F6E3-10CM** F6E3-10DM** F6E3-10EM** F6E3-10FM**	62.5/125um OM1	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
FXE3-10AM** FXE3-10BM** FXE3-10CM** FXE3-10DM** FXE3-10ME** FXE3-10MF**	10 GbE 50/125um OM3	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	20dB	ELECTRIC IVORY	0.30dB	26dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F9E3-10AM** F9E3-10BM** F9E3-10CM** F9E3-10DM** F9E3-10EM** F9E3-10FM**	9/125um OS1	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	YELLOW	0.75dB	55dB	BLUE	0.35dB	55dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE

** - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX SC TO KEYED LC CONFIGURATION CUSTOMER DRAWING		
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477		
										 THIRD ANGLE PROJECTION		
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (0.8) ANGLES		
										DRAWING FILENAME M02779CR_DC_00A.prt		
										SCALE NONE		
										PART NO. SEE TABLE		
R	10-25-07	MC	RELEASED TO PRODUCTION				02779-51			DATE 10-01-07		
REV	DATE	BY	CHK	DESCRIPTION				ECN	R	CUST	SUP	OTH
										CHK'D AS NOTED		
										DRAWING NO. 02779-51 (SHT. 2 of 2)		
										SIZE A		