



01	03-02-06	JH		RELEASED TO PRODUCTION	02055-51				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

RISER RATED - FSDR948Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
1320 N (300 lbf)	330 N (74 lbf)	325 mm (12.8 in)	185 mm (7.3 in)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	INSTALLATION/OPERATION		STORAGE
18.4mm Dia. (.72")	-20° C TO +50° C -4° F TO +122° F		-40° C TO +65° C -40° F TO +149° F

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. CABLE SUPPLIED IN 2500 METER (8202 FT) LENGTHS.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

PANDUIT TM
CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ± .010 (0.3)
(.XX) ± .03 (0.8) ANGLES

DRAWING FILENAME	M02055BH_DC_48-9um_00B.prt
SCALE	NONE

DRAWN BY	MC
DATE	08-28-04
CHK'D	

[illegible]

PART NO.		FSDP948Y FSDR948Y
DRAWING NO.	02055-51	SIZE A

02055-51

SIZE
A

