



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SIMPLEX FIBER OPTIC LC TO LC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
FXF10-10M*Y	RISER (OFNR)	10GbE 50/125um OM3	SIMPLEX 1.6mm	AQUA	0.30dB	26dB	ELECTRIC IVORY
F5F10-10M*Y		50/125um OM2		ORANGE	0.30dB	20dB	ELECTRIC IVORY
F6F10-10M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	ELECTRIC IVORY
F9F10-10M*Y		9/125um OS1		YELLOW	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-04-07	MC		RELEASED TO PRODUCTION	02779-35				

SIMPLEX FIBER OPTIC PATCH CORD LC TO LC CONFIGURATION CUSTOMER DRAWING									
				PANDUIT ™ CORP. TINLEY PARK, ILL 60477					
				ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.005 ANGLES				DRAWING FILENAME M02779CE_DC_00A.prt	
				DRAWN BY MC				SCALE NONE	
				DATE 05-23-07				PART NO. SEE TABLE	
				CHK'D				DRAWING NO. 02779-35 (SHT. 2 of 2)	
								SIZE A	