


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIMENSIONS						WEIGHT
	A (REF)	B (REF)	C	D	E (REF)	F	lbs / 25pcs (kg) / 25pcs
BR-1.5-TW	1.50 [38]	5.91 [150]	0.32 [8] MINIMUM	0.215 [5.45] 0.211 [5.37]	3.64 [93]	2.02 [51.3] 1.98 [50.3]	5.1 (2.3)
BR-2.0-TW	2.00 [51]	6.42 [163]	0.32 [8] MINIMUM	0.215 [5.45] 0.211 [5.37]	3.64 [93]	2.02 [51.3] 1.98 [50.3]	5.5 (2.5)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- RECOMMENDED PASS-THRU HOLE DIAMETER FOR "TOGGLE WING" IS 3/4".

DIMENSIONS IN BRACKETS ARE METRIC [mm]	
CAD FILENAME/LAYERS G03668DZ_DC_GB3668DZ/00A	
TINLEY PARK, ILLINOIS	
BR-_-TW BRIDLE RING TOGGLE CLAMP	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ±5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
DRAWN BY ARHA	MAT'L: LOW CARBON STEEL BRIGHT ZINC ELECTROPLATE
DATE 09-15-09	SCALE NONE
CHK'D KCN	DRAWING NO. GB3668DZ
	DWG A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
OOA	09/15/09	ARHA	<i>AK</i>	INITIAL RELEASE	GB3668DZ	OOA	<i>KCN</i>	