



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

*PANDUIT PART NUMBER	A IN (mm)	B IN (mm)	T IN (mm)	WEIGHT LBS / 100 FT (g)
T12T	.125 (3.2)	.218±.047 (5.5±1.2)	.020±.006 (0.5±0.2)	0.6 (272.2)
T19T	.188 (4.8)	.250±.047 (6.4±1.2)	.030±.008 (0.8±0.2)	1.3 (589.7)
T25T	.250 (6.4)	.375±.047 (9.5±1.2)	.030±.008 (0.8±0.2)	1.9 (861.8)
T38T	.375 (9.5)	.437±.047 (11.1±1.2)	.030±.010 (0.8±0.3)	2.8 (1270.0)
T50T	.500 (12.7)	.500±.047 (12.7±1.2)	.030±.016 (0.8±0.4)	4.1 (1859.7)
T62T	.625 (15.9)	.625±.047 (15.9±1.2)	.030±.020 (0.8±0.5)	5.0 (2267.9)
T75T	.750 (19.1)	.875±.047 (22.2±1.2)	.030±.020 (0.8±0.5)	6.3 (2857.6)
T100T	1.000 (25.4)	1.125±.047 (28.6±1.2)	.040±.020 (1.0±0.5)	11.4 (5158)



- NOTES:
 * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS, PACKAGE SIZE AND PART COLOR
 2) FOR ROLL SIZES LARGER THAN 10 FT., SPLICING MAY OCCUR.
 3) REVERSE CUT

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

CAD FILENAME/LAYERS G01322BA_G00239DL_PB_FLRPPOLYWRAP_05/07B



CORP. TINLEY PARK, ILLINOIS

FLUOROPOLYMER SPIRAL WRAP

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
4	5/10/11	LEF	VJS	ADDED NOTES	GB0239DL	4	RAMI	
3	1/17/97	RJKO		ADDED T19T TO TABLE	GB0239DL	3		

DRAWN BY CJG	DATE 6/5/96	MAT'L: FLUOROPOLYMER	DRAWING NO. GB0239DL	DWG A
CHK'D JVL				SIZE