





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
NKHS2**-X	.06 LB/10 PCS (29.1 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME		M02201BC_NKHS2_00.PRT	SIZE A
DRAWING FILENAME		M02201BC_DC_00A.PRT	
NETKEY™ 2 POSITION SLOPED INSERT CUSTOMER DRAWING			
 PANDUIT™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER		N/A
	PRODUCT SPEC		N/A
	WORK INSTRUCTION		N/A
	SCALE		NONE
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±		
DRAWN BY JsP	MATERIAL: ABS		PART NO. NKHS2**-X
DATE 3-30-05			
CHK'D			DRAWING NO. 02201-06

R	3-30-05	JsP		RELEASED TO PRODUCTION	02201-06				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH