


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NYLON 6/6 COLOR NUMBER SUFFIX *	POLYPROPYLENE COLOR NUMBER SUFFIX *	"A" STRAP COLOR	"B" STRIPE COLOR
1-10	101-10	BROWN	WHITE
3-10	103-10	ORANGE	
5-10	105-10	GREEN	
6-10	106-10	BLUE	
8-10	108-10	SLATE	
1-2	101-2	BROWN	RED
3-2	103-2	ORANGE	
5-2	105-2	GREEN	
6-2	106-2	BLUE	
8-2	108-2	SLATE	
1-0	101-0	BROWN	BLACK
3-0	103-0	ORANGE	
5-0	105-0	GREEN	
6-0	106-0	BLUE	
8-0	108-0	SLATE	
1-4	106-4	BROWN	YELLOW
3-4	103-4	ORANGE	
5-4	105-4	GREEN	
6-4	106-4	BLUE	
8-4	108-4	SLATE	
1-7	101-7	BROWN	VIOLET
3-7	103-7	ORANGE	
5-7	105-7	GREEN	
6-7	106-7	BLUE	
8-7	108-7	SLATE	
0	100	BLACK	SOLID COLOR CABLE TIES
1	101	BROWN	
2	102	RED	
3	103	ORANGE	
4	104	YELLOW	
5	105	GREEN	
6	106	BLUE	
8	108	SLATE	

PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	MINIMUM LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT (W/O RIBBON) lbs (g) 100 pcs
	MIN IN (mm)	MAX IN (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)			
PLT1M-L*	.06 (1.5)	.82 (21)	.036 (.9)	.100 (2.5)	.175 (4.4)	.154 (3.9)	.185 (4.7)	4.0 (102)	18 (80)	MINIATURE	.06 (29)

NOTES:

SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES
STRIPED PLT1M SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(.25) (.XXX) ± .020(.51)
(.XX) ± .02(.5) ANGLES ± -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
CEW

MAT'L:

SCALE
NONE

8 2-17-04 JABO

NUMERICALLY ORGANIZED CHART
ADDED SOLID COLORS 1, 3, 5, 6, & 8

2333 8

DATE
9-17-85

SEE TABLE

DRAWING NO.
SS-2333

DWG
A
SIZE

REV DATE BY CHK DESCRIPTION ECN - R CUST SUP

CHK'D
HVP