



190356-000 | JM-SIM-21S057SB

Jackmoon Fiber Optic Simplex Duct Plug, Size 2.10, for up to 1 cable with outer diameter between 8.9 and 14.5 mm

- Anchors and organizes subducts or multiple duct systems
- Eliminates duct-edge abrasion to cables
- Excellent for supporting cables at the tops of risers
- Expandable gasket allows for expansion and contraction of cables or subducts without leakage
- Split design for retrofitting without disassembly

Product Classification

Brand	Jackmoon®
Product Type	Duct plug, simplex fiber
Regional Availability	EMEA Latin America North America

Body Features

Body Material	PVC
Body Style	Round
Color	White

Configuration Features

Number of Cable Attachments	1
Size Type	2.10

Dimensions

Inner Duct diameter, minimum	50.30 mm		1.98 in
Cable Diameter, maximum	14.50 mm		0.57 in
Cable Diameter, minimum	8.90 mm		0.35 in
Inner Duct Diameter, maximum	55.40 mm		2.18 in

Operation/Application

Environment	Handholes Manholes
For Use With	Cables Pipes Subducts

Usage Conditions

Weather Resistance	5m waterhead
--------------------	--------------

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------