



64674072-00 | 6467 4 072-00

FMK Series Modular Jack, 8-position, RJ45, category 5e, T568A/B, bag of 10, white

- High speed data and voice transmission outlets
- Suitable for direct termination of 1000 twisted pair insulated copper wires
- Compatible with the LSA-PLUS® insertion tool and 110 punchdown tool

OBSOLETE

This product was discontinued on: March 30, 2018

Replaced By

760238472

SL FMK Series Modular Jack, RJ45, Category 6, white

Product Classification

Product Series	FMK
Product Type	Modular jack
Regional Availability	Australia/New Zealand

Electrical Specifications

Transmission Standard	ANSI/TIA-568-C.2 ISO/IEC 11801 Class D
-----------------------	------------------------------------------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Color	White
Package Quantity	10
Packaging Type	Bag
Panel Thickness, recommended	1.60 mm

Mechanical Specifications

Conductor Gauge, solid	24–22 AWG
Conductor Gauge, stranded	26–24 AWG
Conductor Type	Solid Stranded
Material Type	Polycarbonate
Outlet Type	Standard
Plug Insertion Life, minimum	2500 times
Rear Termination Punchdowns, minimum	200 times

64674072-00 | 6467 4 072-00

Rear Termination Type	IDC
Wiring	T568A T568B

Mechanical Specifications

Rear Termination Tool	LSA-PLUS Punchdown tool
-----------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant