



64674072-10 | 6467 4 072-10

**FMK Series Modular Jack, 8-position, RJ45, category 5e, T568A/B, bag of 10, black**

- High speed data and voice transmission outlets
- Suitable for direct termination of 1000 twisted pair insulated copper wires
- Compatible with the LSA-PLUS® insertion tool and 110 punchdown tool

## **OBSOLETE**

This product was discontinued on: **March 30, 2018**

### **Replaced By**

760238471

SL FMK Series Modular Jack, RJ45, Category 6, black

## **Product Classification**

Product Series	FMK
Product Type	Modular jack
Regional Availability	Australia/New Zealand

## **Electrical Specifications**

Transmission Standard	ANSI/TIA-568-C.2   ISO/IEC 11801 Class D
-----------------------	--

## **Environmental Specifications**

Flammability Rating	UL 94 V-0
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Relative Humidity	Up to 93%, non-condensing
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

## **General Specifications**

Cable Type	U/UTP (unshielded)
Color	Black
Package Quantity	10
Packaging Type	Bag
Panel Thickness, recommended	1.60 mm

## **Mechanical Specifications**

Conductor Gauge, solid	24–22 AWG
Conductor Gauge, stranded	26–24 AWG
Conductor Type	Solid   Stranded
Material Type	Polycarbonate
Outlet Type	Standard
Plug Insertion Life, minimum	2500 times
Rear Termination Punchdowns, minimum	200 times
Rear Termination Type	IDC

64674072-10 | 6467 4 072-10

Wiring T568A | T568B

## Mechanical Specifications

Rear Termination Tool LSA-PLUS Punchdown tool

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant