

108333022 | M10LE-270

## M10LE-270 Gray Faceplate

### Product Classification

Portfolio	CommScope®
Product Type	Faceplate kit
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

### General Specifications

Color	Gray
Mount Type	Flush
Total Ports, quantity	1
Application	Used with the M-Type modular information outlets
Package Quantity	1

### Dimensions

Depth	8.38 mm   0.33 in
Height	72.14 mm   2.84 in
Width	122.17 mm   4.81 in
Weight	0.04 kg   0.09 lb

### Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL   UL

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system