



760075069 | M81C Coupler
M81C Coaxial Coupler, almond

Product Classification

Portfolio	CommScope®
Product Type	Multimedia coupler
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Application	Module designed for video applications
Color	Almond
Mount Type	Snap-in
Package Quantity	1

Dimensions

Depth	12.70 mm 0.50 in
Height	17.53 mm 0.69 in
Width	18.54 mm 0.73 in

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

