

760100867 | M11SP

M11SP 1-port Single Gang Stainless Steel Faceplate

Product Classification

Portfolio	CommScope®
Product Type	Faceplate kit
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Mount Type	Flush
Total Ports, quantity	1
Application	Used with M-Series modular information outlet
Package Quantity	1

Dimensions

Depth	4.06 mm 0.16 in
Height	114.30 mm 4.50 in
Width	69.85 mm 2.75 in

Mechanical Specifications

Material Type	Stainless steel
---------------	-----------------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system