



760117994 | MFC-SCF-09-6X-25

**OptiSPEED® Fiber Qwik II-SC Connector™, field installable, beige, 25 Pack**

## Product Classification

Portfolio	CommScope®
Brand	OptiSPEED®
Product Type	Fiber connector
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

Fiber Type	OM1
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia

## Dimensions

Compatible Cable Diameter	0.9 mm   0.0 in
Length	50.20 mm   1.98 in

## General Specifications

Interface	SC
Body Style	BTW
Interface Feature	Field Installable   Mechanical splice
Color	Beige
Package Quantity	25

## Mechanical Specifications

Cable Retention Strength, maximum	0.45 kg @ 0 ° 1.00 lb @ 0 °
-----------------------------------	--------------------------------

## Optical Performance

Insertion Loss, typical	0.40 dB
Return Loss, minimum	20.0 dB

## Optical Specifications

Optical Components Standard	ANSI/TIA-568-C.3
-----------------------------	------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant

# Product Specifications



760117994 | MFC-SCF-09-6X-25

ISO 9001:2008      Designed, manufactured and/or distributed under this quality management system

