



760031039 | MODG2-12LC-SM-PT

**G2 Modular Cassette with 12 LC TeraSPEED® Single-mode Pigtails**

## **OBSOLETE**

Replaced By

760109496

360G2 Cassette 12-LC-SM-BL-Pigtails

SYSTIMAX 360G2 Cassette 12 LC TeraSPEED® Blue with Pigtails iPatch Ready

## Product Classification

Portfolio	SYSTIMAX®
Brand	TeraSPEED®
Product Type	Fiber cassette with pigtails
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED®   OS2
Total Fibers, quantity	12

## Dimensions

Depth	119.38 mm   4.70 in
Height	30.48 mm   1.20 in
Pigtail Length	1.5 m   4.9 ft
Width	91.44 mm   3.60 in

## Environmental Specifications

Safety Standard	UL
-----------------	----

## General Specifications

Interface, front	LC
Adapter Color	Blue
Brand	SYSTIMAX®
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	12

## Optical Performance

Insertion Loss, typical	0.30 dB
Return Loss, minimum	55.0 dB

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

## Included Products

- 860278613 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, blue, 1.5 m
- 760095596 | X-TB-8W-BL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
  - 760211201 | X-TB-8G-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860278621 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, orange, 1.5 m
- 760095604 | X-TB-8W-OR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
  - 760211219 | X-TB-8G-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860278639 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, green, 1.5 m
- 760095612 | X-TB-8W-GR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278647 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, brown, 1.5 m
- 760095620 | X-TB-8W-BR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278654 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, slate, 1.5 m
- 760095638 | X-TB-8W-SL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278662 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, white, 1.5 m
- 760095646 | X-TB-8W-WH-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278670 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, red, 1.5 m
- 760095653 | X-TB-8W-RD-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 860278688 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, black, 1.5 m

760031039 | MODG2-12LC-SM-PT

- 760095661 | X-TB-8W-BK-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278696 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, yellow, 1.5 m

- 760038570 | X-TB-8W-YL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode
- 760200568 | X-TB-8G-YL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber

860278704 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, violet, 1.5 m

- 760095679 | X-TB-8W-VI-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278712 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, rose, 1.5 m

- 760095687 | X-TB-8W-RS-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

860278720 (Product Component—not orderable) — TeraSPEED® LC 0.9 mm Pigtail, aqua, 1.5 m

- 760095695 | X-TB-8W-AQ-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 460125289 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode

760049809 | SFA-LC12-BL-SHUTTERED — TeraSPEED® LC Multiport Shuttered Adapter, Blue, Single Pack