



760032268 | MODG2-6SC-SM-PT-A

G2 Modular Cassette with 6 SC TeraSPEED® Single-mode Pigtails, Type A

OBSOLETE

Replaced By

760109553

360G2 Cassette 6-SC-SM-BL-Pigtails A SYSTIMAX 360G2 Cassette 6 SC TeraSPEED® Blue with Pigtails A

Product Classification

Portfolio	SYSTIMAX®
Brand	TeraSPEED®
Product Type	Fiber cassette with pigtails
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	6

Dimensions

Depth	119.38 mm 4.70 in
Height	30.48 mm 1.20 in
Pigtail Length	1.5 m 4.9 ft
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
-----------------	----

General Specifications

Interface, front	SC
Adapter Color	Blue
Brand	SYSTIMAX®
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	6

Optical Performance

Insertion Loss, typical	0.40 dB
Return Loss, minimum	55.0 dB

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

- 860240670 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, blue, 1.5 m
- 760095596 | X-TB-8W-BL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
 - 760211201 | X-TB-8G-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860240688 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, orange, 1.5 m
- 760095604 | X-TB-8W-OR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
 - 760211219 | X-TB-8G-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860240696 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, green, 1.5 m
- 760095612 | X-TB-8W-GR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
- 860240704 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, brown, 1.5 m
- 760095620 | X-TB-8W-BR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
- 860240712 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, slate, 1.5 m
- 760095638 | X-TB-8W-SL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
- 860240720 (Product Component—not orderable) — TeraSPEED® SC 0.9 mm Pigtail, white, 1.5 m
- 760095646 | X-TB-8W-WH-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode
- 760049783 | SFA-SC06-BL-SHUTTERED — TeraSPEED® SC Multiport Shuttered Adapter, Blue, Single Pack