



760202556 | 360-iP-1100A-E-GS6-1U-24

**SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Angled Patch Panel, 24 port**

## Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch®   SYSTIMAX 360™
Product Type	Copper patch panel
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Depth	266.70 mm   10.50 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	44.45 mm   1.75 in
Weight	0.82 kg   1.80 lb
Width	482.60 mm   19.00 in

## Electrical Specifications

ANSI/TIA Category	6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA   CE   ETL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Intelligence Type	iPatch® enabled
Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Brand	iPatch®   SYSTIMAX 360™   SYSTIMAX®
Color	Cool gray
Includes	Cable management bar   Four "A" labels   Four #12-24 mounting screws   Instruction sheet   Panel   Twenty-four

Package Quantity	cable ties 1
------------------	-----------------

## Mechanical Specifications

Panel Style	Angled
Material Type	ABS   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf   133 N
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2008	