



CPC3316-01 | GS8E-R-BK

GigaSPEED XL® GS8E Stranded Cordage Rollover Modular Patch Cord, Black Jacket

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED XL®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Black
Brand	GigaSPEED XL® SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf

Wiring

Rollover

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	Brown
Position 2	Orange	Lt. Brown
Position 3	Lt. Green	Green
Position 4	Blue	Lt. Blue
Position 5	Lt. Blue	Blue
Position 6	Green	Lt. Green
Position 7	Lt. Brown	Orange
Position 8	Brown	White/Orange

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2008

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

860014141 | 1074E BK 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 1074E Category 6 U/UTP Cable, non-plenum, black jacket, 4 pair count, variable length, reel

860533850 | 2074E BK 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 2074E Category 6 U/UTP Cable, plenum, black jacket, 4 pair count, variable length, reel