



CPC3392-07 | GS8E-L-RD

**GigaSPEED XL® GS8E Stranded Low Smoke Zero Halogen Cordage Modular Patch Cord, Red Jacket**

## Product Classification

|                       |                                                                     |
|-----------------------|---------------------------------------------------------------------|
| Portfolio             | SYSTIMAX®                                                           |
| Brand                 | GigaSPEED XL®                                                       |
| Product Type          | Twisted pair patch cord                                             |
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Dimensions

|                      |               |
|----------------------|---------------|
| Cord Length, maximum | 30 m   100 ft |
| Cord Length, minimum | 1 m   1 ft    |

## Electrical Specifications

|                        |          |
|------------------------|----------|
| ANSI/TIA Category      | 6        |
| dc Resistance, maximum | 0.30 ohm |
| Safety Voltage Rating  | 300 V    |

## Environmental Specifications

|                       |                                      |
|-----------------------|--------------------------------------|
| Environmental Space   | Low Smoke Zero Halogen (LSZH)        |
| Flammability Rating   | UL 94 V-0                            |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |

## General Specifications

|                                |                           |
|--------------------------------|---------------------------|
| Cable Type                     | U/UTP (unshielded)        |
| Interface, connector A         | RJ45 plug                 |
| Interface, connector B         | RJ45 plug                 |
| Jacket Color                   | Red                       |
| Brand                          | GigaSPEED XL®   SYSTIMAX® |
| Interface Feature, connector A | Standard                  |
| Interface Feature, connector B | Standard                  |
| Package Quantity               | 1                         |
| Pairs, quantity                | 4                         |

## Mechanical Specifications

|                               |                              |
|-------------------------------|------------------------------|
| Conductor Type                | Stranded                     |
| Material Type                 | Copper alloy   Polycarbonate |
| Outlet/Module Contact Plating | Precious metals              |
| Plug Insertion Life, minimum  | 750 times                    |
| Plug Retention Force, minimum | 133 N   30 lbf               |
| Wiring                        | T568B                        |

## Wiring Diagram

|            | Connector A  | Connector B  |
|------------|--------------|--------------|
| Position 1 | White/Orange | White/Orange |
| Position 2 | Orange       | Orange       |
| Position 3 | Lt. Green    | Lt. Green    |
| Position 4 | Blue         | Blue         |
| Position 5 | Lt. Blue     | Lt. Blue     |
| Position 6 | Green        | Green        |
| Position 7 | Lt. Brown    | Lt. Brown    |
| Position 8 | Brown        | Brown        |

## Regulatory Compliance/Certifications

| Agency          | Classification                                                                 |
|-----------------|--------------------------------------------------------------------------------|
| RoHS 2011/65/EU | Compliant                                                                      |
| ISO 9001:2008   | Designed, manufactured and/or distributed under this quality management system |



## Included Products

860498625 | 3074E RD 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 3074E Category 6 U/UTP Cable, low smoke zero halogen, red jacket, 4 pair count, variable length, reel

- 860018639 | 1074E RD 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 1074E Category 6 U/UTP Cable, non-plenum, red jacket, 4 pair count, variable length, reel