



CPC3482-02 | GS8E117-S-LB

GigaSPEED XL® GS8E Single End Solid Cable Modular Patch Cord, Light Blue Jacket

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED XL®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	100 m 300 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	Unterminated
Jacket Color	Light blue
Brand	GigaSPEED XL® SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568B

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	
Position 2	Orange	
Position 3	Lt. Green	
Position 4	Blue	
Position 5	Lt. Blue	
Position 6	Green	
Position 7	Lt. Brown	
Position 8	Brown	

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

860062678 | 1071E LB 4/23 RVAR (Product Component—not orderable) — GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, light blue jacket, 4 pair count, variable length, reel