



CPC5412-03 | VP117-P8GS-DG

GigaSPEED XL® VisiPatch® Single-ended 4-pair Patch Cord, Dark Gray Jacket

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED XL® VisiPatch®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	VisiPatch®
Interface, connector B	Unterminated
Jacket Color	Dark gray
Brand	GigaSPEED XL® SYSTIMAX® VisiPatch®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals

CPC5412-03 | VP117-P8GS-DG

Plug Insertion Life, minimum 200 times
Plug Retention Force, minimum 44 N | 10 lbf
Wiring VisiPatch®

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	
Position 2	Blue	
Position 3	White/Orange	
Position 4	Orange	
Position 5	Lt. Green	
Position 6	Green	
Position 7	Lt. Brown	
Position 8	Brown	

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

860017029 | 1074E DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 1074E Category 6 U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel