



CPC8662-03 | 119P2PS-DG  
**110 to D8PS 1 Pair Hybrid Patch Cord, Dark Gray Jacket**

## Product Classification

Portfolio	CommScope®
Product Type	Twisted pair patch cord
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   1 ft

## Electrical Specifications

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm

## Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

## General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	110 plug
Interface, connector B	RJ45 plug
Jacket Color	Dark gray
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	1

## Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	18 N   4 lbf
Wiring	110

## Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	
Position 2	Blue	
Position 3		
Position 4		Blue
Position 5		Lt. Blue
Position 6		
Position 7		
Position 8		

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

848202800 | 1074C DG 1/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 1 pair count, variable length, reel