



CPCF392-02 | VP360-GS8E-L-LB

GigaSPEED XL® VisiPatch® 360 to Gs8E 4-pair Low Smoke Zero Halogen Hybrid Patch Cord, light blue jacket

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED XL® VisiPatch 360®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	100 ft 30 m
Cord Length, minimum	1 ft 1 m

Electrical Specifications

ANSI/TIA Category	6
-------------------	---

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
---------------------	-------------------------------

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	VisiPatch® 360
Interface, connector B	VisiPatch® 360
Jacket Color	Light blue
Brand	GigaSPEED XL® SYSTIMAX® VisiPatch® 360
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
Wiring	T568B

Wiring Diagram

	Connector A	Connector B
Position 1	Blue	White/Orange
Position 2	Lt. Blue	Orange
Position 3	Orange	Lt. Green
Position 4	White/Orange	Blue
Position 5	Green	Lt. Blue
Position 6	Lt. Green	Green
Position 7	Brown	Lt. Brown
Position 8	Lt. Brown	Brown

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2008

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

860498641 | 3074E LB 4/24 RVAR (Product Component—not orderable) — GigaSPEED XL® 3074E Category 6 U/UTP Cable, low smoke zero halogen, light blue jacket, 4 pair count, variable length, reel