



CPCFFXD-03 | VP360T-VP360T-P8X10D-XD-DG

GigaSPEED X10D® VisiPatch® 360 to VisiPatch® 360 4 Pair Solid Patch Cord Crossover, Dark Gray Jacket

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D® VisiPatch 360®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	2 m 7 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	VisiPatch® 360
Interface, connector B	VisiPatch® 360
Jacket Color	Dark gray
Brand	GigaSPEED X10D® SYSTIMAX 360™ SYSTIMAX® VisiPatch® 360
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Solid
----------------	-------

CPCFFXD-03 | VP360T-VP360T-P8X10D-XD-DG

Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N 10 lbf
Wiring	VisiPatch® 360 crossover

Wiring Diagram

	Connector A	Connector B
Position 1	Blue	Brown
Position 2	Lt. Blue	Lt. Brown
Position 3	Orange	Green
Position 4	White/Orange	Lt. Green
Position 5	Green	Orange
Position 6	Lt. Green	White/Orange
Position 7	Brown	Blue
Position 8	Lt. Brown	Lt. Blue

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

860474246 | 1095B DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel