



CPCGGJ2-03 | G10FP-DG

**GigaSPEED X10D® G10FP on 1295 Solid F/UTP Cordage, F/UTP Modular Patch Cord, Dark Gray Jacket**

## **OBSOLETE**

This product was discontinued on: May 1, 2018

### Replaced By

CA111H2-0C  
G10SP-GY

GigaSPEED X10D® G10SP on S/FTP Cordage, S/FTP Modular Patch Cord, Gray Jacket

## Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	Twisted pair patch cord
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Cord Length, maximum	100 m   300 ft
Cord Length, minimum	1 m   3 ft

## Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

## Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

## General Specifications

Cable Type	F/UTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Dark gray
Brand	GigaSPEED X10D®   SYSTIMAX 360™   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1

CPCGGJ2-03 | G10FP-DG

Pairs, quantity 4

## Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating Type	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

860382563 | 1295A DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 1295A Category 6A F/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel

860556968 | 1295A OR 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 1295A Category 6A F/UTP Cable, non-plenum, orange jacket, 4 pair count, variable length, reel