Product Specifications





CPCGGL2-04 | G10FP-L-GN

GigaSPEED X10D \circledast G10FP on 3295 Solid Low Smoke Zero Halogen F/UTP Cordage F/UTP Modular Patch Cord, spring green jacket

OBSOLETE

This product was discontinued on: May 1, 2018

Replaced By

CA111K2-0M G10SP-L-GR GigaSPEED X10D® G10SP on S/FTP Low Smoke Zero Halogen Cordage, S/FTP Modular Patch Cord, Green Jacket

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	100 m 300 ft
Cord Length, minimum	1 m 3 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)	
Flammability Rating	UL 94 V-0	
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)	

General Specifications

Cable Type	F/UTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Red
Brand	GigaSPEED X10D® SYSTIMAX 360™ SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Product Specifications



CPCGGL2-04 | G10FP-L-GN

Mechanical Specifications

Conductor Type	Solid	
Material Type	Copper alloy Polycarbonate	
Outlet/Module Contact Plating Type	Precious metals	
Plug Insertion Life, minimum	750 times	
Plug Retention Force, minimum	30 lbf 133 N	
Wiring	Т568В	

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU ISO 9001:2008 Classification Compliant



Included Products

860524479 | 3295A GR 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, green jacket, 4 pair count, variable length, reel
860559566 | 3295A BL 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, blue jacket, 4 pair count, variable length, reel
860559574 | 3295A YL 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, yellow jacket, 4 pair count, variable length, reel
860567296 | 3295A OR 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, orange jacket, 4 pair count, variable length, reel
860567304 | 3295A LL 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, orange jacket, 4 pair count, variable length, reel
860567304 | 3295A LL 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, orange jacket, 4 pair count, variable length, reel
860567304 | 3295A LL 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, lilac jacket, 4 pair count, variable length, reel

Designed, manufactured and/or distributed under this quality management system