

**CPCSSX2-01 | 360GS10E-BK****GigaSPEED X10D® 360GS10E Solid Cordage Modular Patch Cord, Black Jacket**

## Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	Twisted pair patch cord
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Cord Length, maximum	100 ft   30 m
Cord Length, minimum	1 m   3 ft

## Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

## Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

## General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Black
Brand	GigaSPEED X10D®   SYSTIMAX 360™   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

## Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

**Agency**RoHS 2011/65/EU  
ISO 9001:2008**Classification**Compliant  
Designed, manufactured and/or distributed under this quality management system

## Included Products

860474287 | 1095B BK 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, black jacket, 4 pair count, variable length, reel