

## FBMSCUC11

### OptiSPEED® SC to Unconnectorized, Fiber Pigtail, 0.9 mm Riser - SBJ

#### Product Classification

Portfolio	CommScope®
Brand	OptiSPEED®
Product Type	Fiber pigtail, simplex
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

#### Construction Materials

Fiber Type	OM1
Total Fibers, quantity	1

#### Dimensions

Cord Length, maximum	23 ft   7 m
Cord Length, minimum	2 ft   1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

#### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)   Riser
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

#### General Specifications

Construction Type	Pigtail, jacketed
Interface, connector A	SC
Interface Feature, connector A	Standard
Color, connector A	Beige
Interface, connector B	Unterminated

#### Mechanical Specifications

Cable Retention Strength, maximum	2.00 lb @ 90 ° 5.00 lb @ 0 °
-----------------------------------	---------------------------------

#### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



#### Included Products

N-001-RF-6F-F09 (Product Component—not orderable) — OptiSPEED® 0.9mm Low Smoke Zero Halogen Reinforced

FBMSCUC11

---

## Buffered Fiber Cable

- CS-6F-TB (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber

460125834 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, multimode