

FFMLULU62

**OptiSPEED® LC UniBoot to LC UniBoot, Fiber Patch Cord, 2.0 mm Duplex Interconnect , LSZH**

## Product Classification

Portfolio	CommScope®
Brand	OptiSPEED®   UniBoot®
Product Type	Fiber patch cord, duplex
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

Fiber Type	OM1
Total Fibers, quantity	2

## Dimensions

Cord Length, maximum	999 ft   999 m
Cord Length, minimum	2 ft   1 m
Diameter Over Jacket	2.00 mm   0.08 in
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

## Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

## General Specifications

Color, connector A	Beige
Color, connector B	Beige
Construction Type	Duplex patch cord
Interface, connector A	LC
Interface, connector B	LC
Interface Feature, connector A	UniBoot
Interface Feature, connector B	UniBoot

## Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## Included Products

---

N-002-MP-6F-F20 (Product Component—not orderable) — OptiSPEED® Low Smoke Zero Halogen Riser Light Duty Interconnect Cable, 2 fiber

- CS-6F-MP (Product Component—not orderable) — OptiSPEED® OM1 Multimode Fiber

460135312 (Product Component—not orderable) — LazrSPEED® Pre-Radius LC UniBoot for 2.0mm Interconnect Fiber, multimode