

FFWLULU62

TeraSPEED® LC UniBoot to LC UniBoot, Fiber Patch Cord, 2.0 mm Duplex Interconnect , LSZH

Product Classification

Portfolio	CommScope®
Brand	ReadyPATCH® TeraSPEED®
Product Type	Fiber patch cord, duplex
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	2

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	2 ft 1 m
Diameter Over Jacket	2.00 mm 0.08 in
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Color, connector A	Blue
Color, connector B	Blue
Construction Type	Duplex patch cord
Interface, connector A	LC
Interface, connector B	LC
Interface Feature, connector A	Uniboot
Interface Feature, connector B	Uniboot

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



FFWLULU62

Included Products

N-002-MP-8W-F20 (Product Component—not orderable) — TeraSPEED® Low Smoke Zero Halogen Riser Light Duty Interconnect Cable, 2 fiber

- CS-8W-MP (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber

460135221 (Product Component—not orderable) — TeraSPEED® Pre-Radius LC UniBoot for 2.0mm Interconnect Fiber, single-mode