

AXIS T8524 PoE+ Network Switch

24-port switch for efficient network management

AXIS T8524 PoE+ Network Switch is an easy to install 24-port managed Gigabit switch - a perfect complement to Axis' recorders to further simplify setup and installation of surveillance systems. AXIS T8524 comes with an integrated DHCP server for automatic assignment of IP addresses and discovery of connected Axis devices. The intuitive administrator interface offers a graphic topology for easy overview of all devices in the system with information about connected devices and status. The high PoE power output allows for connection of up to 24 PoE cameras.

- > 30 W PoE per port, total 370 W
- > Gigabit switch
- > 2 SFP/RJ45 Combination Ports
- > Intuitive graphic topology for system overview



AXIS T8524 PoE+ Network Switch

Network	
Network function	DHCP server included VLAN
Security	Password protection, IP address filtering, HTTPS encryption, IEEE 802.1X network access control, ACL, Private VLANs, DHCP Snooping
Supported protocols	IPv4, IPv6, HTTP, HTTPS, QoS, Bonjour, UPnP, SNMP v1/v2c/v3, DNS, NTP, TCP, UDP, IGMP, ICMP, DHCP, ARP, SSH, STP, RSTP, MSTP, LLDP, LLDP-MED, TFTP, SMTP, BPDU
Throughput	38.7 Mpps
Switching capacity	52 Gbps
MAC table	8 K
Jumbo frames	9216 Bytes
General	
Casing	Metal Color: Black
Environment	Indoor
Dimensions	442 (W) x 211 (D) x 44 (H) mm 17.4 (W) x 8.31 (D) x 1.73 (H) in
Weight	3.2 kg (7.05 lbs)
Power requirements	100–240 V AC, 50/60 Hz
PoE class	Power over Ethernet Plus (PoE+) IEEE 802.3at Type 2 Class 4
PoE output	Port 1 to 24: Up to 30 W Power budget: 370 W
Connectors	PoE ports RJ45 10Base-T/100Base-TX/1000Base-T (24x)

	Uplink Combination port RJ45/SFP 100Base-TX/1000Base-T (2x) Power Power connector port
Surge protection	6kV on all network ports and AC lines
Operating conditions	0 °C to 50 °C (32 °F to 122 °F) Humidity 10–90% RH (non-condensing)
Storage conditions	-10 °C to 70 °C (14 °F to 158 °F) Humidity 5–95% RH (non-condensing)
Approvals	EMC EN 55032 Class A EN 55024 FCC part 15 Subpart B Class A VCCI Class A RCM AS/NZS CISPR 32 Class A ICES-003 Class A Safety IEC/EN/UL 60950-1 EAC CE, ITE, JATE, SASO, BSMI
Management software	Axis Camera Management
Included accessories	Installation Guide Power cord Rubber feet (4x) 19" ear rack kit
Warranty	Axis 3-year warranty, see www.axis.com/warranty
Environmental resp	onsibility:

www.axis.com/environmental-responsibility

©2017 - 2018 Axis Communications AB. AXIS COMMUNICATIONS, AXIS, and VAPIX are registered trademarks or trademark applications of Axis AB in various jurisdictions. All other company names and products are trademarks or registered trademarks of their respective companies. We reserve the right to introduce modifications without notice.

