


— CUT-THRU FOR # 10 TRUSS HEAD SCREW.



PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	COLOR	UL LISTED* RATED LOAD lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/ 100 PIECES(g)
	MIN. in (mm)	MAX. in (mm)									
HLTP2I -X0	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	BLACK	40 (178)	INTERMEDIATE	.43 (196)
HLTP2I -X12	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	MAROON	40 (178)	INTERMEDIATE	.43 (196)
HLTP3I -X0	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	BLACK	40 (178)	INTERMEDIATE	.62 (282)
HLTP3I -X12	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	MAROON	40 (178)	INTERMEDIATE	.62 (282)

1) HLTP TIES ARE AVAILABLE IN BLACK AND MAROON ONLY.

- * 2) MINIMUM 2" (50.8 mm) OVERLAP REQUIRED TO ACHIEVE UL LISTED RATED LOAD. (1 IN² OR 645 mm²)

CAD FILENAME/LAYERS										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										TAK-TY HOOK & LOOP CABLE TIES HLTP SERIES FLAMMABILITY RATING: UL 94-V2	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .030 (.XX) ± .125 ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY KET	MAT'L: POLYPROPYLENE HOOK/ NYLON KNIT LOOP
										DATE 12/29/98	DRAWING NO. SS-27182
										CHK'D HVP	DWG SIZE A
5	2/3/10	JABO	TGS	CORRECTED HLTP2/31-X0 UL LISTED RATED LOAD	SS-27182	5	TGS				
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP		