


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PLT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PLT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PLT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2223)
PLT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PLT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

						TITLE PAN-TY®NON-RELEASABLE - LASHING TIES									
						CUSTOMER DRAWING									
						ITEM REVISION NAME W10001EG/00		PANDUIT							
						DATASET FILE NAME W10001EG/00-SS-6512_REV09									
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .1 (2.5) .xxx ± .010 (.25) .xx ± .02 (1.5) ANGLES: ---		MATERIAL: NYLON 6/6							
						THIRD ANGLE PROJECTION		DRAWING NUMBER: SS-6512							
						DRAWN BY L.VALDES		DATE 7-15-77		CHK HVP		SCALE NONE		SIZE A	
						REV		DATE		BY		CHK		APR	
						DESCRIPTION		ECN							