



Polycom® VVX® Business Media Phones Portfolio

The Polycom family of VVX series business media phones offer high-quality audio and video communications experience for busy professionals.

Entry Level

The Polycom® VVX® 101 business media phone is a one-line SIP phone for a home office or shared/common areas delivering enterprise grade sound quality.



Application targets

Home office or shared/common areas, such as lobbies, hallways and break rooms

- 1 line
- LCD screen
- G.722 support up to 7 kHz on all audio paths (speaker, handset, headset)
- 1/100 ethernet
- Hard Keys: 12-key dialpad, home, speaker, mute, headset, volume
- 4-way navigation cluster with center “select” key

Entry Level

The Polycom® VVX® 201 business media phone is a two-line SIP for small businesses and medium-sized organizations phone that delivering Polycom® HD™ Voice technology.



Application targets

Ideal for retail environments, call centers or shared/common areas, such as lobbies, hallways and break rooms

- 2 line
- LCD screen
- Polycom HD Voice up to 7 kHz on all audio paths (speaker, handset, headset)
- 2 x ethernet 10/100
- Hard Keys: 12-key dialpad, home, speaker, mute, headset, volume
- 4-way navigation cluster with center “select” key

Basic

The Polycom® VVX® 300 Series business media phone is a powerful entry-level phone for today's cubicle workers handling a low to moderate volume of calls delivering crystal clear communications.



Application targets

Common areas, dorm rooms, wall-mounted deployments, cubicle, office desk

- 6 lines or speed dials
- 208 x 104 pixel resolution
- Polycom HD Voice up to 7 kHz on all audio paths (speaker, handset, headset)
- 2 x Ethernet 10/100 for network pass-through (VVX 300/301)
- 2 x GigE 10/100/1000 for high-performance network pass-through (VVX 310/311)
- Asian character support
- Hard Keys: 12-key dialpad, home, speaker, mute, headset, volume, messages, hold, transfer
- 4-way navigation cluster with center “select” key
- Supports Polycom® VVX® Expansion Module and Polycom® VVX® Color Expansion Module (expandability up to 3 modules)

Mid-range

The Polycom® VVX® 400 Series business media phone is a color mid-range business media phone is designed for today's office workers and attendant consoles delivering crystal clear communications.



Application targets

SOHO, call center, cubicle, office desk

- 12 lines or speed dials
- 3.5” color TFT
- 320 x 240 pixel resolution
- Polycom HD Voice up to 7 kHz on all audio paths (speaker, handset, headset) and Acoustic Fence(TM) technology
- 2x Ethernet 10/100 for network pass-through (VVX 400/401)
- 2x GigE 10/100/1000 for high-performance network pass-through (VVX 410/411)
- RJ9 Headset support with electronic hook switch
- Asian character support
- Hard Keys: 12-key dialpad, home, speaker, mute, headset, volume, messages, hold, transfer
- 4-way navigation cluster with center “select” key
- Supports Polycom VVX Expansion Module and Polycom VVX Color Expansion Module (expandability up to 3 modules)
- 1 x USB for headset connectivity, storage and call recording (VVX 401 and 411)

Performance

The Polycom® VVX® 500 Series is a performance business media phone that delivers best-in-class desktop productivity and unified communications for busy professionals.



Application targets

Knowledge worker, busy professional's office, call center

- 12 lines appearances or speed dials
- 320 x 240 pixel resolution
- 3.5" color touch screen
- Immersive capacitive touch UI
- Video playback and video conferencing via USB camera accessory
- Streaming media video playback
- Full browser
- Polycom HD Voice up to 14 kHz on all audio paths (speaker, handset, headset) and Acoustic Fence technology
- 2x GigE 10/100/1000 for high-performance network pass-through
- RJ9 Headset support with electronic hook switch
- 2 x USB ports
- Business applications integration
- Supports Polycom VVX Expansion Module and Polycom VVX Color Expansion Module (expandability up to 3 modules)
- Video conferencing via optional USB camera

Executive

The Polycom® VVX® 600 Series UC executive business media phone delivers rich voice and applications experience for busy corporate executives and managers.



Application targets

Executive, knowledge worker, busy professional's office

- 16 lines appearances or speed dials
- 480 x 272 pixel resolution
- 4.3" color touch screen
- Polycom® HD Voice™ and Acoustic Fence™ technology
- Immersive, capacitive touch UI
- Video playback and video conferencing via external USB camera
- 2x GigE 10/100/1000 for high-performance network pass-through
- 2 x USB 2.0 host
- RJ9 Headset support with electronic hook switch
- Asian character support
- Business applications integration
- Microsoft® Lync® interoperability
- Supports Polycom VVX Expansion Module and Polycom VVX Color Expansion Module (expandability up to 3 modules)
- Bluetooth support for wireless headset connectivity

Wireless

The Polycom® VVX D60 Wireless Handset is a cost-effective scalable, SIP-based, on premise, mobile communications system



Application targets

VVX DECT solution is ideal for busy users who need to be reachable whether they are at their desk or elsewhere in their immediate workspace.

- Support pairing up to 5 DECT handsets (for VVX 300, 400, 500 and 600) and 1 DECT handset (VVX 101 and VVX 201)
- Provisioning and Management through host phone via Ethernet
- 2" TFT (178x220) color display with backlit LCD
- Support for 4 simultaneous calls
- HD Voice support
- Range: 50m(165ft) indoor/300m(980ft) outdoor
- 10/100 POE Base Station with Pass-through
- DECT 1.92GHz - 1.93GHz (US), 1.88GHz-1.90GHz (EU)
- 10 hours talk time, 100 hours standby
- Dedicated 2.5 mm headset port (external 2.5mm to 3.5mm adapter)

VVX video accessory

The Polycom® VVX® Camera is a high quality USB video camera, designed as an easy add-on that complements the Polycom VVX 500 or VVX 600 desktop phones. The Polycom VVX Camera enables busy professionals to collaborate interactively with the best in class personal video communications experience.



Application targets

Executive, knowledge workers, busy professionals

- High quality business grade video
- Transmits Polycom HD Video resolution (720 p 30 fps) H.264 compression
- Matches elegantly look and feel of the VVX 500 and VVX 600
- Camera lens shutter for privacy
- Lens mechanical adjustability to change camera angle for eye-level video calls
- USB plug-and-play
- Flexible—for use with VVX phone

Expansion modules

The Polycom® VVX® expansion modules turn your VVX business media phone into a high-performance attendant console.



Application targets

Telephone attendant's desk, front desk, team manager's desk
Compatible with Polycom VVX 300/310, 400/410, 500 and 600

Paper-based

- 40 multifunctional line keys configurable as line registration, call appearance, speed dial, DSS, or BLF
- Dual-color (red or green) illuminated LEDs for line status information

LCD-based

- 4.3 in. LCD (480 x 272 pixel resolution)
- Color graphical user interface
- 28 multifunctional line keys configurable as line registration, call appearance, speed dial, DSS, or BLF
- Dual-color (red or green) illuminated LEDs for line status information
- 3 page keys for additional line appearances (up to 84 in total)

Expandability

- Up to three VVX Expansion Modules can be attached to any VVX phone
- Provided by Polycom VVX host phone
- Host phone powering options: IEEE 802.3 (af/at) PoE or using a compatible external AC adapter
- Power

Executive

The Polycom® VVX® 1500 executive business media phone combines advanced IP telephony, one-touch video, and business applications into a seamless, life-like experience.



Application targets

Busy executive, knowledge worker, busy professional's office

- 6 lines/speed dials (shared call/bridged line appearance)
- Capable of displaying multiparty video conferences
- Resistive touch screen interface (UI) (7-inch color touch display)
- One-touch speed dial, redial
- Busy Lamp Field (BLF)
- Local three-way audio conferencing
- Polycom HD Voice quality (up to 20 kHz with G.719 support) in all modes: handset, speakerphone and headset for both voice and video
- 2 x ethernet 10/100/1000
- 2 x USB 2.0 host
- Business applications integration
- Microsoft Lync interoperability
- High quality business grade video
- Video resolution is up to VGA (640 x 480)
- Supports H.263, H.263+, and H.264
- Optional H.323 license purchasable

Executive

The Polycom® VVX® 1500 D executive business media phone is an easy-to-use, dual-stack business media phone for H.323 and SIP environments.



Application targets

Busy home office worker/executive

- 6 lines/speed dials (shared call/bridged line appearance)
- Capable of displaying multiparty video conferences
- Resistive touch screen interface (UI) (7-inch color touch display)
- Local three-way audio conferencing
- One-touch speed dial, redial
- Busy lamp field (BLF)
- Dual-stack H.323 and SIP simultaneously running
- Local three-way audio conferencing
- Polycom HD Voice quality (up to 20 kHz with G.719 support) in all modes: handset, speakerphone and headset for both voice and video
- 2 x ethernet 10/100/1000
- 1 x USB 2.0 host
- Business applications integration
- Microsoft Lync interoperability
- High quality business grade video
- Video resolution is up to VGA (640 x 480)
- Supports H.263, H.263+, and H.264

Need flexible financing?

Polycom **CAPITAL**
Collaborative Financing

www.polycom.com/polycom-capital

About Polycom

Polycom helps organizations unleash the power of human collaboration. More than 400,000 companies and institutions worldwide defy distance with video, voice and content solutions from Polycom. Polycom and its global partner ecosystem provide flexible collaboration solutions for any environment that deliver the best user experience and unmatched investment protection.

Polycom, Inc.
1.800.POLYCOM
www.polycom.com

Polycom Asia Pacific Pte Ltd
+65 6389 9200
www.polycom.com.sg

Polycom EMEA
+44 (0)1753 723282
www.polycom.co.uk

