









## Polycom Conference Phone Guide

IP conference phones	Large room		Standard conference room			Small room and office
	Polycom Trio™ 8800 	Polycom® SoundStation® IP 7000 	Polycom Trio™ 8500 	Polycom® SoundStation® Duo 	Polycom® SoundStation® IP 6000 	Polycom® SoundStation® IP 5000 
<b>Call platform connectivity</b>						
IP (SIP)	•	•	•	•	•	•
Skype for Business/Office 365/Lync	•		•	Lync only		Lync only
Analog				•		
<b>Voice quality</b>						
Polycom® HD Voice™ technology	•	•	•	•	•	•
Loudspeaker frequency response	100 Hz - 22 kHz	160 Hz—22 kHz	180 Hz—14 kHz	220 Hz—7 kHz	220 Hz—14 kHz	250 Hz—7 kHz
Microphone pickup range	6 m/20 ft	6 m/20 ft	4.2 m/14 ft	3 m/10 ft	3.6 m/12 ft	2 m/7 ft
Intelligent microphone mixing	•	•	•	•	•	•
Dynamic noise reduction	•	•	•	•	•	•
Polycom® NoiseBlock™	•		•			
Automatic gain control	•	•	•		•	
<b>Additional features</b>						
Resists interference from wireless devices	•	•	•	•	•	
Software upgradable	•	•	•	•	•	
Large display to support advanced applications		•				
Large color touch screen user interface	•		•			
Multi-unit connectivity		•				
Connect to external audio system	•	• <sup>(1)</sup>	•			
Computer/mobile device connectivity	•	•	•			
Wi-Fi network connectivity <sup>(2)</sup>	•					
Bluetooth enabled	•		•			
<b>Optional accessories</b>						
Expansion microphones (wired)	•	•	•	•	•	
Wireless lapel pin microphone		• (NA only)			• (NA only)	
Video integration kit or cables		•				
Computer calling kit				•		
Mobile device cables		•		•		
Polycom Trio™ Visual+ (enables content and video capability)	•		•			
Power Kit	•		•			
<b>Model variants</b>						
SIP/PoE only	2200-66070-001	2200-40000-001	2200-66700-025		2200-15600-xxx	2200-30900-025
AC or Power over Ethernet (PoE)		2230-40300-001		2200-19000-xxx	2200-15660-xxx	2200-30900-xxx
Skype for Business/O365/Lync (PoE)	2200-66070-019		2200-66700-019			
Optional AC power supply	7200-23490-xxx	•	2200-66740-xxx	•	•	•

<sup>1</sup> Optional accessory required

<sup>2</sup> Available when used as a conference phone only (not for use with Polycom Trio Visual+)

Analog conference phones	Standard conference room		Small room and office
	Polycom® SoundStation2™ 	Polycom® SoundStation® Duo 	Polycom® VoiceStation® 300 
<b>Network connectivity</b>			
Analog	•	•	•
IP (SIP)		•	
Microsoft Lync		•	
<b>Voice Quality</b>			
Polycom HD Voice technology		•	
Loudspeaker frequency response	300 Hz–3300 Hz	220 Hz–7 kHz	300 Hz – 3300 Hz
Microphone pickup range	3 m/10 ft	3 m/10 ft	2 m/7 ft
Intelligent microphone mixing	•	•	•
Dynamic noise reduction	•	•	•
Automatic gain control			
<b>Additional Features</b>			
Resists interference from wireless devices	•	•	•
Software upgradable		•	
Large display to support advanced applications			
Multi-unit connectivity			
Connect to external audio system	•		
Bluetooth connectivity			
<b>Optional accessories</b>			
Expansion microphones (wired)	• <sup>(3)</sup>	•	
Wireless lapel pin microphone	•		
Video integration kit or cables			
Computer calling kit	• <sup>(3)</sup>	•	
Mobile device cables	• <sup>(3)</sup>	•	
<b>Model variants</b>			
	2200-15100-xxx (non expandable w/o display)	2200-19000-xxx	2200-17910-xxx
	2200-16000-xxx (non-expandable, w/ display)		
	2200-16200-xxx (expandable, w/display)		

<sup>3</sup> Available on selected models

Bluetooth/USB Speakerphones	Small room, office, and portable
	<p>Polycom® VoxBox™</p> 
Call platform / client connectivity	
IP (SIP)	UC client on connected device
Cellular service	Via connected smartphone
Skype for Business and Skype	UC client on connected device
RealPresence Desktop/Mobile	UC client on connected device
Leading UC client apps	UC client on connected device
BYOD Audio I/O, Web apps	Via connected PC, tablet or smartphone sound settings
Voice Quality	
Polycom® HD Voice™ technology	•
Loudspeaker frequency response	200 Hz - 14 kHz
Microphone pickup range	3 m/10 ft
Intelligent microphone mixing	•
Dynamic noise reduction	•
Polycom® NoiseBlock™	•
Automatic gain control	•
Additional features	
Resists interference from wireless devices	•
Companion App	•
Software upgradeable	•
Touch interface (no screen)	•
IP64 Dust and Water resistance	•
Cast aluminum enclosure	•
Multi-unit connectivity	
Connect to external audio	
Computer/mobile device Connectivity	•
Wi-Fi network connectivity	
Bluetooth enabled	pairing with 2 devices, remembers 10 devices
USB	•
Battery	6.5 hours talk time
Power	Charge via USB
Portable	•
Carrying case	included
USB cables	1.2m/4 ft USB and 3 m/10 ft USB security cable included

## About Polycom

Polycom helps organizations unleash the power of human collaboration. More than 400,000 companies and institutions worldwide defy distance with video, voice and content solutions from Polycom. Polycom and its global partner ecosystem provide flexible collaboration solutions for any environment that deliver the best user experience and unmatched investment protection.

Polycom, Inc.  
1.800.POLYCOM  
[www.polycom.com](http://www.polycom.com)

Polycom Asia Pacific Pte Ltd  
+65 6389 9200  
[www.polycom.com.sg](http://www.polycom.com.sg)

Polycom EMEA  
+44 (0)1753 723282  
[www.polycom.co.uk](http://www.polycom.co.uk)

