C-FL-A-RTF2/RTS2 Series

Premium LED Floodlight - Large

Replaces 250W PSMH



MAKE AN IMPRESSION FOR LESS!

Premium LED Floodlight - Large is nearly half the cost of our High-Output LED Floodlights, and is sure to impress with light ouputs up to 13,900 lumens and multiple beam spreads



PRODUCT SPECIFICATIONS

OVERVIEW

• Initial Delivered Lumens: 12,300-13,900

• CRI: ≥ 70

CCT: Neutral White (4000K), Cool White (5000K)

• Input Power: 118 Watts

· Dimmable: No

• Distribution: 90° Flood (Wide), 40° Flood (Narrow)

• Operating Minimum: -40°C (-40°F)

• Lifespan: Estimated >100,000 Hours

Power Factor: > 0.9

Total Harmonic Distortion: < 20%

Limited Warranty: 5 Years*

· Replaces 250W PSMH

EFFICIENT	FLEXIBLE	RECOMMENDED USE	INPUT VOLTAGE
Uses 57% less energy than comparable PSMH fixturessEnjoy up to 12% more light	• Wide beam angles (40°/90°) for use in a wide variety of applications	Building FacadesSecurityUplighting for Signs & Displays	• Universal (120V through 277V Operation)

ORDERING INFORMATION

Example: C-FL-A-RTF2-12L-40K-DB


C-FL-A				DB
PRODUCT	STYLE	LUMEN PACKAGE	CCT	COLOR
C-FL-A	RTF2 Premium Floodlight, 90° Flood (Wide)	12L 12.400 Lumens, 50K only 12.300 Lumens, 50K only 118W	40K Neutral White (4000K) 50K Cool White (5000K)	
	RTS2 Premium Floodlight, 40° Flood (Narrow)	13L 13.900 Lumens, 50K only 13.600 Lumens, 40K only 118W		

CERTIFICATIONS:





C-FL-A-RTF2/RTS2 Series



SERIES OVERVIEW

DIMENSIONS	PRODUCT WEIGHT	MOUNTING HEIGHT
7-3/8" L x 12-3/4" W x 14-5/8" H	13.8 lbs.	15 to 25 feet

FIXTURE SPECIFICATIONS

HOUSING	Low-copper, die-cast aluminum housing and lens frame Dark bronze polyester powder-coat finish	
LENS ASSEMBLY	Tempered glass lens is thermal, shock and impact resistant Polycarbonate reflector	
MOUNTING	Includes 2" adjustable fitter	

ELECTRICAL PERFORMANCE

OPERATING MINIMUM	LIFESPAN L ₇₀ at 25°C (77°F)	POWER FACTOR	TOTAL HARMONIC Distortion	DIMMABLE
-40°C (-40°F)	Estimated >100,000 Hours	> 0.9	< 20%	No
INPUT VOLTAGE	120V	208V	240V	277V
CURRENT DRAW (Amps)	0.98A	0.57A	0.49A	0.43A

WARRANTY AND CERTIFICATIONS

WARRANTY	UL LISTED
5 Year Limited*	Wet Locations



C-FL-A-RTF2/RTS2 Series

ACCESSORIES



PHOTOCELL - BUTTON, 120V/208V/240V/277V

SKU: **C-ACC-A-PCELL-LV** (120V) **C-ACC-A-PCELL-HV-TL** (208V/240V/277V))

USE: Photocell is field installed

