

Technical drawing of a laser inkjet label. The label is rectangular with a white imprint area on the left and a clear area on the right. The drawing includes dimensions and tolerances for the label's size and the spacing of the inkjet labels.

Dimensions and Tolerances:

- Overall height: $8.5 \pm .062$ [216 ± 1.6]
- Overall width: $11.0 \pm .062$ [279 ± 1.6]
- White imprint area width: $.25 \pm .062$ [6.35 ± 1.6] TYP. 13 PLCS.
- Clear area width: $.75 \pm .062$ [19.05 ± 1.6] TYP. 13 PLCS.
- Label height: $.50 \pm .062$ [12.70 ± 1.6] TYP. 13 PLCS.

Labels are arranged in a grid pattern. The drawing includes a "PRINTER LEAD EDGE FEED IN THIS DIRECTION" arrow pointing to the left and a "LASER INKJET LABELS 5050X075VJ" label.

PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEET QTY.	STANDARD PKG. QTY.
S050X075YAJ	6MY6 CLEAR POLYESTER FILM	0.500 [12.7] X 0.750 [19.0]	169	30	5000

CAD FILENAME/LAYERS		100472BZ_DC_C10200/02C	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
CUSTOMER DRAWING OPTIMUM SELF-LAM. LASER INKJET PRINTABLE LABELS			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU	MAT'L; SEE TABLE	SCALE NTS	
DATE 9/22/04		DRAWING NO. C10200	
CHK'D		A SIZE	