


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	COLOR (PMS)	LABELS SHEET	SHEET QTY.	STD. PKG. QTY.		
S100X225YAJ	GMY6 CLEAR POLYESTER FILM	1.000 [25.4] X 2.250 [57.2]	WHITE	32	32	1000		
S100X225YBJ			BLUE (291C)					
S100X225YCJ			BROWN (465C)					
S100X225YDJ			GREEN (353C)					
S100X225YEJ			GRAY (422C)					
S100X225YFJ			ORANGE (150C)					
S100X225YGJ			PURPLE (264C)					
S100X225YHJ			RED (184C)					
S100X225YIJ			YELLOW (101C)					
S100X225YAJ-D			WHITE				16	500
S100X225YBJ-D			BLUE (291C)					
S100X225YDJ-D			GREEN (353C)					
S100X225YHJ-D			RED (184C)					
S100X225YIJ-D			YELLOW (101C)					

CAD FILENAME/LAYERS 100472CF_DC_C10206/00A

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING OPTIMUMM SELF-LAM.
LASER INKJET PRINTABLE LABELS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	8-12-08	RVU		CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.	5516	R		
1	9-12-06	RVU		ADDED PART NUMBER WITH -D.	4680	R		
0	6-29-06	RVU		DRAWING RELEASE. MAT'L WAS GMY2.	4568	R		
A	9-22-04	RVU		ENGRG. RELEASE.	0000	R		

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1 (.XXX) ± .025
(.XX) ± .050 ANGLES ±



UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RVU
DATE
9/22/04
CHK'D

MAT'L:
SEE TABLE

SCALE
NTS
DRAWING NO.
C10206
DWG
A
SIZE