


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES. UNLESS OTHERWISE SPECIFIED:
PANDUIT CT-100A
TOOL WEIGHT: 7.2 oz. (205 g)
WIRE CUTTER for NO. 10 AWG and smaller copper wire.
CRIMPING DIES for Pan-Term insulated terminals, disconnects, splices and wire joints on No. 22 to 10 AWG stranded wire.
CUTTERS for machine screws of sizes shown.
CRIMPING DIE for Pan-Term non-insulated terminals, disconnects, splices and wire joints on No. 22 to 10 AWG solid or stranded wire.
CRIMP POCKETS A and B for additional terminals and disconnects per instructions on product packaging.
WIRE STRIPPER for removing plastic or rubber wire insulation. Strip length should allow a minimum of 1/32" of conductor to extend beyond terminal barrel.
DIMENSIONS IN PARENTHESES ARE (mm).

										PANDUIT CORP. TINLEY PARK, ILLINOIS		
										CT-100A Crimping Tool		
										Customer Drawing		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± .1 (.xxx) ± .05 (.xx) ± .05 ANGLES ± .05		
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN MILLIMETERS, THIRD ANGLE PROJECTION.		
										SCALE: NONE		
										DRAWING NO. TP27597C01		
										DWG. SIZE: C		
00	2-26-15	BLR		RELEASED	4857	---					DRAWN BY: BLR	MATL: -----
REV	DATE	BY	CHK'D	DESCRIPTION	ECN	- R	CUST	SUP			DATE: 2-26-15	CHK'D: