

CATALOG NO.	WIRE RANGE	STUD SIZE	AS-25036	DIMENSIONS				BULK CATALOG NO.	INSTALLATION TOOLING	WIRE STRIP LENGTH	REV	DATE	DESCRIPTION	ECO	BY	CHK
				C	L Max.	Y Max.	Z Max.				B	01/03/2014	UPDATED AS PER MARKUP	34495	SAV	MB
TN18-4	22 - 18 MAX. INSUL. DIA. ACCOM.: 120 COLOR CODE: RED	3-4	-148	.23 [6]	.76 [19]	.64 [16]	.20 [5]	YAES18N48	NON-RATCHET: Y10D, Y1022 RATCHET: MR8-83, MRE1022NV PNEUMATIC: Y6NCP1 WITH J1022NC3 DIES	7/32"						
TN18-6		4-6	-101	.25 [6]	.76 [19]	.64 [16]	.20 [5]	YAES18N1								
TN186G1		4-6	-102	.25 [6]	.87 [22]	.74 [19]	.49 [12]	YAES18N2								
TN18-8		6-8	-149	.31 [8]	.91 [23]	.76 [19]	.29 [7]	YAES18N49								
TN18-10		8-10	-103	.31 [8]	.91 [23]	.76 [19]	.29 [7]	YAES18N3								
TN18-14		12,1/4	-150	.46 [12]	1.09 [28]	.87 [22]	.41 [10]	YAES18N50								
TN18-516		5/16	-104	.46 [12]	1.09 [28]	.87 [22]	.41 [10]	YAES18N4								
TN18-38		3/8	-105	.53 [14]	1.17 [30]	.91 [23]	.45 [11]	YAES18N5								
TN14-4	16 - 14 MAX. INSUL. DIA. ACCOM.: 153 COLOR CODE: BLUE	3-4	-152	.25 [6]	.79 [20]	.67 [17]	.24 [6]	YAES14N52	7/32"							
TN14-6		4-6	-106	.25 [6]	.79 [20]	.67 [17]	.24 [6]	YAES14N6								
TN146G1		4-6	-107	.30 [8]	.91 [23]	.76 [19]	.51 [13]	YAES14N7								
TN14-8		6-8	-153	.31 [8]	.89 [23]	.74 [19]	.31 [8]	YAES14N53								
TN14-10		8-10	-108	.31 [8]	.89 [23]	.74 [19]	.31 [8]	YAES14N8								
TN14-14		12,1/4	-154	.45 [11]	1.08 [27]	.86 [22]	.43 [11]	YAES14N54								
TN1412		1/2	---	.69 [18]	1.43 [36]	1.10 [28]	.62 [16]	YAES14N55								
TN14-516		5/16	-109	.45 [11]	1.08 [27]	.86 [22]	.43 [11]	YAES14N9								
TN14-38	3/8	-110	.53 [14]	1.16 [30]	.90 [23]	.47 [12]	YAES14N10									
TN10-6	12 - 10 MAX. INSUL. DIA. ACCOM.: 210 COLOR CODE: YELLOW	4-6	-111	.37 [9]	1.12 [28]	.94 [24]	.26 [7]	YAES10N11	11/32"							
TN10-8		6-8	-156	.37 [9]	1.12 [28]	.94 [24]	.26 [7]	YAES10N56								
TN10-10		8-10	-112	.37 [9]	1.12 [28]	.94 [24]	.26 [7]	YAES10N12								
TN10-14		12,1/4	-157	.53 [14]	1.32 [34]	1.06 [27]	.37 [9]	YAES10N57								
TN10-516		5/16	-113	.53 [14]	1.32 [34]	1.06 [27]	.37 [9]	YAES10N13								
TN10-38		3/8	-114	.58 [15]	1.34 [34]	1.05 [27]	.40 [10]	YAES10N14								

NOTES:

- MATERIAL:
TERMINAL: COPPER.
INSULATION: NYLON.
- FINISH:
TERMINAL: TIN PLATED.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		INSULUG™	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: TN-- (SEE TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: M.RAMESH 10/19/2012	
		CHECKER: E.MARTIN 10/31/2012	
		DSN APRVL: E.MARTIN 10/31/2012	
		MFG APRVL: --	
		QA APRVL: C. ACKERMAN 12/4/2012	
		MKT APRVL: S.GALE 11/17/2012	
		PROD FAM: CM&R	
		DRAWING NO	
		50010506	
		REV	
		B	
		SHEET 1 OF 1	