DRAWING NO.
SD206499-01

REV	DATE	DESCRIPTION	ECO	BY	CHK.
B	08/13/2013 00:00:00 AM	NOTE 5 'S' FEAS 'S' ADDED FOR TIN PLATING.	32843	BD	MA

CATALOG NUMBER [5]	I.P.S. PIPE ACCOMMODATED			COPPER CABLE ACCOMMODATED		H	J	W	RECOMMENDED TIGHTENING TORQUE
	NOMINAL O.D.	ACTUAL O.D. (in)	ACTUAL O.D. [mm]	AWG	METRIC WIRE SIZE				
GAR3902	1/2"-1"	.840-1.32	[22-33]	4 STR(.232)-4/0 STR(.528)	$25mm^2$ STR[6.6]-$95mm^2$ STR[12.9]	3.50 [89]	3/8"-16"	3.25 [83]	200 Lb*in [22.5 N*m]
GAR3903	1-1/4"-2"	1.66-2.38	[43-60]			4.00 [102]		4.25 [108]	
GAR3904	2-1/2"-3-1/2"	2.88-4.00	[74-101]			6.50 [165]		6.00 [152]	
GAR3905	4"-5"	4.50-5.56	[115-141]			7.50 [191]		7.50 [191]	
GAR3906	6"	6.62	[168]			8.50 [216]		8.62 [219]	
GAR3907	8"	8.62	[218]			10.00 [254]		10.62 [270]	
GAR3908	10"	10.75	[273]			12.00 [305]		12.75 [324]	
GAR3909	12"	12.75	[323]			14.00 [356]		14.75 [375]	





NOTES:

1. MATERIAL: AS NOTED.
2. UL 467 LISTED, FILE NO. E9999. ACCEPTABLE FOR DIRECT BURIAL.
3. CSA C22.2 NO. 65 LISTED, FILE NO. 42862.
4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.

[5] ADD SUFFIX "TN" TO THESE CATALOG NUMBERS FOR TIN-PLATED VERSIONS.

REV: PE0200

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: http://www.burndy.com

GAR ASSEMBLY

ITEM NO:	--		
CAT. NO:	GAR390- (TABLE)		
DRAWN BY:	MP	11/20/90	BURNDY
CHECKER:	ATM	11/20/90	
DSN APPVL:	KW	11/20/90	
MFG APPVL:	--	--	
QA APPVL:	AL	11/20/90	
MKT APPVL:	--	--	SCALE: 1:1
PROD FAM:	SUBSTATION		DRAWING NO: SD206499-01 REV: B
PROJECT #:	--	SIZE: D	
DOCUMENT TYPE:	Sales		
REL LEVEL:	Released		SHEET 1 OF 1