



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

GAR114C  
 7818102310055  
 8-4CU 1/4IPS  
 Active

**Web Use**  
 BURNDY Product Line

Width (in)  
 Length (in)  
 Height (in)  
 Size (Hex) or Size (Bolt)  
 Size (Hex) or Size (Bolt) - in  
 B Length (in)  
 Width (Fraction)  
 Height (Fraction) (in)

**Dimensional**  
 1.88  
 1.31  
 2.50  
 3/8  
 0.38  
 1.50  
 1-7/8  
 2-1/2

**Product Description**

Ground Clamp-Cable to Rebar, 8 Sol. - 4 Str., Bright Dipped

**Type of U Bolt**

**General**  
 271

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards  
 Rated for Direct Burial

**Approvals / Certifications**

Y  
 Y  
 Exempt  
 N  
 N  
 UL467  
 Y

Copper Tube Size (SCH40) - Range  
 Rod Size (Range)  
 Copper Solid Size (Range)  
 Copper Stranded (Range)  
 Rebar Size (Range)

**Conductor(s)**  
 1/4 IPS IPS  
 1/2 in  
 8 AWG-3 AWG  
 9 AWG-4 AWG  
 N/A

Type of Hardware  
 Installation Torque  
 Type of Plating  
 Plated (Yes or No)  
 Product Material

**Physical**  
 DURIUM& Silicon Bronze  
 240  
 Bright Dipped  
 N  
 Copper Alloy

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175