



BURNDY Catalog Number
UPC Number
Description
Status

GAR1834
 7818102354099
 300-500CU 2 IPS
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 4.06
 Length (in) 2.38
 Height (in) 5.25
 Size (Hex) or Size (Bolt) 1/2
 Size (Hex) or Size (Bolt) - in 0.50
 B Length (in) 2.75
 Width (Fraction) 4-1/8
 Height (Fraction) (in) 5-1/4

General

Mechanical Grounding Connector,
 Cable to Rod or Pipe, 300 - 500
 kcmil, 2" to 2-3/8" Rod, 2" Pipe,
 Bright Dipped

Other

260

Approvals / Certifications

Product Description

Type of U Bolt

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards
 Rated for Direct Burial

Y
 Y
 Exempt
 N
 N
 UL467
 Y

Conductor(s)

Copper Tube Size (SCH40) - Range
 Rod Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)
 Rebar Size (Range)

2 IPS IPS
 2 in-2 3/8 in
 N/A
 300 kcmil-500 kcmil
 N/A

Physical

Type of Hardware
 Installation Torque
 Type of Plating
 Plated (Yes or No)
 Product Material

DURIUM® Silicon Bronze
 480
 Bright Dipped
 N
 Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175