



BURNDY Catalog Number
UPC Number
Description
Status

GG182
7818102600811
2 BRAID TO 2 IPS
Active

Web Use
BURNDY Product Line

Dimensional

Width (in) 4.06
Height (in) 4.38
Size (Hex) or Size (Bolt) 1/2
Braid Max Width (in) 2.00
Braid Max Width (Fraction) 2
Size (Hex) or Size (Bolt) - in 0.50
B Length (in) 1.75
Width (Fraction) 4-1/8
Height (Fraction) (in) 4-3/8

General

Product Description

Mechanical Grounding Connector,
Copper Bar, Strap, Braid or Cable
to Rod or Tube, 2" Pipe, 2"-2
3/8" Rod, 4.06 IN Width

Conductor(s)

Copper Tube Size (SCH40) - Range 2-2-1/4
Rod Size (Range) 2 in

Physical

Installation Torque 480
Type of Plating Unplated
Plated (Yes or No) N
Product Material Copper Alloy
Screw Material Type DURIUM® Silicon Bronze

Approvals / Certifications

UL Listed N
CSA Certified Y
ROHS Compatible Exempt
UL Recognized N
CULUS N
Industry Standards UL467
Rated for Direct Burial Y

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175