



BURNDY Catalog Number
UPC Number
Description
Status

KSU27
7818100367099
SERVIT UNIV 1-3/0
Active

Web Use
BURNDY Product Line

Dimensional

Width (in) 1.12
Cross Flats 1.38

General

Product Description

Tin-plated, high strength copper alloy SERVIT[®] with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors.

Conductor(s)

Copper Tap Range 8 AWG-3/0 AWG
CopperWeld Solid Run Size (Range) N/A
Copper Stranded Run (Range) 1 AWG-3/0 AWG
CopperWeld Stranded Tap Size (Range) N/A
Copper Solid Tap (Range) 8 AWG
CopperWeld Solid Tap Size (Range) N/A
Copper Solid Run Size (Range) 22
CopperWeld Stranded Run Size (Range) N/A

Physical

Installation Torque 500
Type of Plating Tin - Electro Plated
Connector Type Split Bolt
Plated (Yes or No) Y
Product Material Copper

Approvals / Certifications

UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175