



BURNDY Catalog Number
UPC Number
Description
Status

KVSU34
7818100833077
UNIV OKLIP 400-500/4-500
Active

Web Use
BURNDY Product Line

Product Description

General

Tin-plated copper alloy connector with tin plated silicon bronze hardware. Spacer bar separates dissimilar conductors and provides long contact length.

Conductor(s)

Aluminum Run Size (Range) 400 kcmil-500 kcmil
Copper Tap Range 4 AWG-500 kcmil
CopperWeld Solid Run Size (Range) -
Copper Stranded Run (Range) 400 kcmil-500 kcmil
CopperWeld Stranded Tap Size (Range) #4 - 4/0
CopperWeld Solid Tap Size (Range) #4 - 4/0
Aluminum Tap Size (Range) 4 AWG-500 kcmil
Galvanized Steel Size (Range) 3/4 (19) in
CopperWeld Stranded Run Size (Range) -

Approvals / Certifications

UL Listed N
CSA Certified Y
ROHS Compatible Exempt
UL Recognized N
CULUS N

Physical

Installation Torque 375
Type of Plating Tin
Plated (Yes or No) Y
Product Material Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175