



BURNDY Catalog Number
UPC Number
Description
Status

TP1010F
 7818107108833
 FORK 10- 12 AWG
 Active

Web Use
 BURNDY Product Line

Dimensional	
Max Insulation Diameter	0.26
Length (in)	1.07
Tongue Type	Fork
Thickness	0.04
B Length (in)	0.34
Pad Width (in)	0.41
Strip Length	19/64
Electrical	
Max Voltage Rating	600
General	
Product Description	Copper Terminal, Fork Tongue, 12-10 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated
Other	
Bulk Package	*BA10EF10M
Physical	
Type of Plating	Tin
Connector Type	Terminal - Fork
Color Code	Yellow
Insulation Type	Vinyl
Plated (Yes or No)	Y
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	12 AWG-10 AWG
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175