



BURNDY Catalog Number

UPC Number

Description

Status

Web Use

BURNDY Product Line

TP1610

7818107148433

RING- 22- 16 AWG- VINYL, 10

STUD

Active

Dimensional

Max Insulation Diameter	0.145
Length (in)	0.85
Tongue Type	Ring
Pad Width (in)	0.31
Strip Length	13/64

Electrical

Max Voltage Rating	600
--------------------	-----

General

Product Description	Copper Terminal, Ring Tongue, 22-16 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated
---------------------	---

Other

Bulk Package	BA16E10M
--------------	----------

Physical

Type of Plating	Tin
Connector Type	Terminal
Color Code	Red
Insulation Type	Vinyl
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Conductor(s)

Copper Solid Size (Range)	20 -16 AWG
Copper Stranded (Range)	20 AWG-16 AWG

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175