



**BURNDY Catalog Number**  
**UPC Number**

YAV14T2BOX  
7818105425077  
RING- 20- 12 AWG-UNIN, QTY  
100  
Active

**Description**  
**Status**

**Web Use**  
BURNDY Product Line

**Dimensional**

Length (in) 0.99  
Tongue Type Ring  
Stud Size (in) 1/4  
Pad Width (in) 0.40  
Strip Length 9/32 "

**General**

Product Description

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Hole, 20-14 AWG, 1/4" Stud, Short Barrel, Tin Plated, Wire strip length:9/32 "

**Other**

Installation Tooling

Non-Ratchet:Y10D, Y10-22  
Ratchet:MR8G98, MR8-9Q, Y8MRB-1, MR20

Bulk Package

YAV14T2

**Approvals / Certifications**

UL Listed Y  
CSA Certified Y  
ROHS Compatible Compliant  
UL Recognized N  
CULUS N  
Industry Standards UL467

**Conductor(s)**

Aircraft Cable Size (Range) N/A  
Copper Solid Size (Range) 20 -14 AWG  
Navy Cable Size (Range) N/A  
Copper Stranded (Range) 20 AWG-14 AWG

**Physical**

Type of Plating Tin - Electro Plated  
Connector Type Terminal - Ring  
Plated (Yes or No) Y

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175